

## Technical Specifications

- Supply voltage..... 230 V / 115 V
- Frequency ..... 50 Hz / 60 Hz
- Power consumption .....400 VA
- Measuring range  
per weighing cell.....500, 1000, 2000 kg
- Measuring accuracy .....± 0.1 % of the end  
value of the measuring range of the weighing cell
- Number of weighing cells  
depending on the application ..... 4, 6, 8

## Applications

Wood based panel industry

- After the press
- Star cooler
- Sanding line
- Panel store (stack scale)

Long-time representation of weight  
and raw density



บริษัท เต็มโซล อินโนเวชัน จำกัด  
341/193 ซ.สุขุมวิท 101/1 แขวงบางจาก  
เขตพระโขนง กรุงเทพมหานคร 10260  
โทร +6684 668 4871  
E-Mail monara@temsolv.com  
www.temsolv.com

Fagus-GreCon

Greten GmbH & Co. KG

Postfach 1234

D-31042 Alfeld-Hannover

Telefon +49(0)5181-79-0

Telefax +49(0)5181-79-229

E-Mail sales@grecon.de

www.grecon.de

# GreCon

Inline Weight  
Measurement with  
the Board Scale

GreCon  
Measuring  
Technology

GreCon  
Fire  
Protection



EN | R.01 | 2013.04  
Subject to technical and country-specific modifications.  
© Fagus-GreCon Greten GmbH & Co. KG

TEMSOL  
GS 5000



## Your Benefit



- Measurement while production is running or standing still
- Can be combined with a thickness gauge to evaluate the raw density
- Elimination of incorrect panel weights, continuous monitoring of the material consumption
- Improved quality control

## Why GreCon



- Application of various weighing cell types
- Vibration-damped radial supports

## Easy Weight Measurement for Reliable Quality Control

The platform weighing scale measures the weights of solid materials, such as wood based panels. Measurement can be conducted both at standstill and during running production. The weight is measured by specially developed radial supports with integrated weighing cells. Depending on the measuring task and the mechanical construction of the weighing table, weighing cells with an optimum measuring range are used.

The preferred use of the weighing system during production is to use a belt conveyor that eliminates vibrations with mechanical dampers, suspension arms and electronic filters that are integrated with the evaluation system. The length of the measured material, transport speed, mechanical dynamics, and electronic running times determine the table length and the weighing time of the scale during production.

The electrical signal which is generated in the weighing cells is pre-processed by a carrier frequency amplifier and then transferred to a control console. Representation and easy operation of the system are done by a touch screen. The weighing data can be sent to a network printer or the data transferred to a process control system. With an optional linkage with a GreCon thickness gauge, the average raw density and the weight distribution within the panels can also be calculated and used to optimise the process.

- ① Board scale with belt conveyor
- ② Radial support



①

②